

8040 RELUMENS

Headlight renovation kit

The applied polymer material is highly transparent and characterized by its strong adhesion. It greatly improves lens appearance & visibility and restores dull, yellowed headlights to like-new clarity. The kit can be used for restoring all types of vehicle headlights and prolonging their lifespan, or it can be applied as extra protection for new car headlights.

OPERATING STEPS:



1. Thoroughly clean the headlight lens and dry with a clean towel.



2. Use masking tape to protect nearby painted surfaces.



3. Sanding. Sand, then wipe off, making sure it is polished right up to the edges. Change the grit after each sanding. P 320 → P 400 → P 500 → P 600 → P 800 - P 1000 → P 1200 - P 1500




4. Wipe off any impurities with a wet towel and dry the lens with a clean dry towel. Now you will have a smooth, even and milky surface. Check thoroughly to ensure there are no sandpaper marks.



5. Add 80–100 ml of headlight restorer liquid to a heating jug and cover with the lid. Heat up the liquid for about 5–6 mins until vapour is starting to come out of the nozzle.



6. Start to apply the vapour 1cm away from the headlight and apply from bottom to top until the headlight is bright. Make sure the pipe orifice is pointing upward to prevent the vapour turning into water drops. Keep your face at least 40cm away from the pipe orifice.



7. 80–100 ml of headlight restorer liquid allows 4–5 min of application time. After application leave the headlight to rest for 10 mins (curing time). Allow the remaining liquid to cool down for 5 mins and pour the remaining liquid back into the bottle.



PRECAUTIONS:

1. Avoid direct sunlight. Store in a well-ventilated place.
2. Please wear a mask while using and DO NOT sniff or drink this product.
3. Keep away from pregnant women and children.
4. Safety data sheet is available on the website.

PACKAGE CONTENTS:

- Headlight restorer polymer
- Heating jug
- Adapter: 100–240V 50/60Hz, 1.6A
- Masking tape
- Instructions for use



SILCO d. o. o.
Šentrupert 5a, 3303 Gomilsko, Slovenia
Tel.: +386 (0)3 703 31 80
info@silco.si, www.silco.si